



Tube unit		Bucky Table (BT-W1)	
Focal size	1.0mm × 2.0mm,	Movement	Longitudinal, ±350mm
	0.6mm × 1.2mm		Transverse, ±150mm
Anode Heat Unit	140kHU, 300kHU	Table Dimensions	2000L×745W×710H
Max kVp	125kVp, 150kVp	* OPTION	
Max mA	300mA/ 500mA/ 600mA	Bucky Stand (BS-W1)	
Collimator (CM-W1)		Dimension	585W × 585D × 1900Hmm
Lightning	26 - 30sec, 100 - 160lux	Grid : Standard	Bucky 85LPI 8:1 fd=40- 72"
Tube Stand (TS-W1)		Ceiling Tube Suspended (TC-W1)	
Left/Right moving available	1,800mm more	Movement	Up/Down, 1200mm
			Longitudinal, 2950mm /
Total height	2,100mm		Transverse, 1750mm
Stand arm swing angle	±90°	Arm Angle	±180°

